



Applicable Requirements :
ANSI/UL 1017
CSA C22.2 No.243

Characteristics



Hydrocart



Activated Carbon



Corrosive Recovery



Accessories Included



Wear Protective Clothing (PPE)



Wet Recovery



- Can be used in the Pharmaceutical industry when equipped with a stainless steel SAE 304 4-wheel dolly or tilting cart
- Designed for the recovery of acids and corrosive liquids
- Heavy duty 2-stage by-pass motor
- Available with a variety of activated carbon, including KINA 3® activated carbon for the adsorption of chloride and acid vapors (HF, HCL, etc). Other types of activated carbon are available. Carbon cartridges must be ordered separately - not included
- For liquid recovery
- Acid-resistant polyethylene, nylon and PVC
- Available with a 4-wheel dolly, tilting cart, or hydro-cart
- 4-wheel dolly, and tilting cart available in stainless steel
- Includes a complete tool kit.

Specifications

2D-ARU-15 SERIES	111429A	111430A
Model Name	2D-ARU-15 (TC) MRAC	2D-ARU-15 STD (HY-C) MRAC
Type (Powerhead)	Electric	Electric
Voltage	120 V	120 V
Hertz	60 Hz	60 Hz
Phase	Single	Single
Wattage	1050 W	1050 W
Power	1.6 HP	1.6 HP
Amperage	10.5 A	10.5 A
Air Flow	110 CFM	110 CFM
Vacuum Pressure	107 " H ₂ O	107 " H ₂ O
Plug Type	120V	120V
Suction Inlet	1.5 "	1.5 "
Cart Type	Tilt Cart (TC)	Hydro Cart (HYC)
Filter Cleaning	None	None
Liquid Recovery Capacity	12.5 gal.	12.5 gal.
Length	27 "	49 "
Width	30 "	20 "
Height	48 "	51 "
Weight (Vacuum Only)	105 lb.	250 lb.
Cord Length	35 ft.	35 ft.

Please note that specifications are subject to change without notice

Use only recommended tools & accessories



ARU STD Tools and Accessories - Included



Liquid Filter - Included



Activated Carbon Cartridge - Optional



2D-ARU-15 STD (HY-C) MRAC