

Contact Us

Products Distributors Brochures

# **WP-82Y**

请使用翻译作用于这页底部以翻译页对汉语。

TPS Australia - Quality hand-made instruments since 1968.

# WP-82Y Waterproof Dissolved Oxygen -**Temperature Meter**



## Full Size Image

The WP-82Y uses the rugged EDYSI Dissolved Oxygen sensor, which can be submersed to 60 metres

- Rugged and Waterproof
- **User-friendly**
- Calendar Clock
- **Good Laboratory Practices**
- 2400 Reading Notepad
- Automatic Datalogging
- RS232 Serial Port Interface
- **Multiple Power Options**
- Australian Made

The WP series enclosure is fully waterproof to IP67 rating. The connectors are rated to IP65. The case, keypad and connectors are designed for maximum durability in the harshest conditions. The WP Series is equally at home in laboratory, field or industrial environments.

The 32 character alphanumeric display features a user-friendly menu system. This guides the user through every step of operation. Full text prompting and error messages are provided. Calibration and set-up are a breeze with the WP Series.

The Calendar Clock can be displayed continuously along with the data. The date and time are recorded with every reading, when using the Notepad and AutoLog functions.

To comply with Good Laboratory Practices (GLP) standards, the WP Series store the date, time and results of the last calibration. This information can be recalled when required. All readings stored in memory are stamped with the date and time.

To reduce errors when recording readings, the WP Series has a 2400 reading Notepad. At the touch of a button, readings can be recorded into memory, along with the date and time. This is especially useful when taking readings in wet environments.

Program the AutoLog function to automatically log readings into memory. Simply set the logging interval from 1 minute to 24 hours, start logging and walk away. The WP Series can log up to 2400 readings, along with the date and time.

The WP Series has RS232 serial port interface. All readings stored in memory and GLP information can be downloaded to a PC or printer. The RS232 serial port also allows the AutoLog function to log directly to a PC or printer. WinTPS Windows software allows the WP Series to communicate with a PC for data download.

The WP Series is supplied with a rechargeable NiMH battery and charger as standard. Chargers for all countries are available. For extended field trips a solar panel, or a charger lead for a car cigarette lighter socket are also available.

The WP Series is proudly designed and manufactured in Australia. Our aim is to provide you with the best quality, service and value for money. The TPS Quality System has been certified in accordance with the AS/NZS ISO 9001 standard. Since 1968, TPS has built a reputation for excellent backup service that is second to none. Compare the list of features with the competition. The WP Series sets a new standard for handheld instruments.

# **Specifications**

ppM (mg/L)
Panges\* : 0.0 to 20.00 ppM Resolution: 0.01 & 0.1 ppM : +/-0.2% of full Accuracy

scale of selected

range

#### % Saturation

Ranges\* : 0 to 240.0 %Sat'n and 240 to 450 %Sat'n Resolution : 0.1 & 1 %Sat'n Accuracy : +/-0.3 %Sat'n

## % Gaseous

Ranges\* : 0 to 45.0 %Gas and 45 to 100 %Gas Resolution : 0.1 & 1 %Gas Accuracy : +/-0.1 %Gas

\*Automatic range selection, subject to sensor performance.

## **Temperature**

: -10.0 to 120.0 °C Range

(sensor limit 45 °C)

Resolution : 0.1 °C : +/-0.2 °C Accuracy

# Salinity Correction

User-set, from 0 to 50.0 ppK NaCl

#### **Barometric Pressure Correction**

User-set, from 800 to 1100 HPa

## Altitude Correction

User-set, from 0 to 5000m

# **Temperature Compensation**

Dual automatic temperature compensation system

#### **Enclosure**

Tough, anti-static Luran-S plastic case, waterproof to IP67. Connectors waterproof to IP65. The instrument will float if dropped into water.

#### Display

32 Character alphanumeric LCD with user-friendly menu system and fulltext messages.

#### Memory

2400 readings, including date and time.

#### Automatic Logging

User-set for one reading every 1 to 90 seconds, 1 to 90 minutes or 1 to 24

#### RS232 Serial Port Output

300, 1200 and 9600 Baud.

8 Bits, No Parity, 1 Stop Bit, XON/XOFF

#### Clock

24 Hour Calendar Clock

### **Battery Saver Function**

On : Automatically switches off after 5 minutes of no use. Off: Unit remains on for continuous

# Good Laboratory Practices

Date, time and results of last successful calibration are stored, and can be recalled when required. GLP information can be printed or downloaded to PC when the optional RS232 Interface is fitted. Warning of failed calibration is provided.

### Power

6V NiMH Rechargeable battery pack for approx 75 hours operation. Battery charger for country of choice supplied. Battery can be charged from any 12V DC source.

#### **Dimensions**

187 x 110 x 51 mm

Instrument only : Approx 440 grams Full Kit : Approx 1.7 kg

#### Environment

Temperature : 0 to 45 °C : 0 to 95% R.H. Humidity

**Ordering Information** 

| Part No                              | Part No                                |
|--------------------------------------|--|
| WP-82Y DO2-Temp 1m123148/1           | Options and Accessories                |
| WP-82Y DO2-Temp 3m123148/3           | oparono ana mococconico                |
| WP-82Y DO2-Temp 5m123148/5           |  |
|                                      | Dissolved Oxygen Sensor Field Stirrer: |
| 4.00 5 ( 0-4 111                     | YSI 5739 DO2 Sensor Stirrer123306      |
| 1, 3 & 5 metre Options Include       | (Separate battery source required)     |
| 1 metre bundle 123148/1:             | BOD Dissolved Oxygen Sensors:          |
| DO2 Sensor YSI5739 (no cable).123204 | YSI non-stirring BOD Sensor123214      |
| 1m cable for Sensor (YSI5739).123212 | (1.5m cable)                           |
| Membrane & filling sol'n kit123300   | YSI self-stirring BOD Sensor123213     |
| 9V Alkaline Battery130026            | (1.5m cable) (Mains power required)    |
| Manual130050                         |  |
| 0                                    | Dissolved Oxygen Sensor Maintenance:   |
| 3 metre bundle 123148/3:             | YSI5739 Field Sensor & Non Stir BOD    |
| DO2 Sensor YSI5739 (no cable).123204 | Membrane & filling sol'n kit123300     |
| 3m cable for Sensor (YSI5739).123221 | Filling Solution only, 45mL123303      |
| Membrane & filling sol'n kit123300   | Zero calibrate Sodium Sulphite.123302  |
| 9V Alkaline Battery130026            | Rejuvenation kit123037                 |
| Manual130050                         | Diaphragm replacement kit123304        |
|                                      | (123304 for YSI5739 Sensor Only)       |
| 5 metre bundle 123148/5:             |  |
| DO2 Sensor YSI5739 (no cable).123204 | YSI Self-Stirring BOD Sensor           |
| 5m cable for Sensor (YSI5739).123222 | Membrane Cap Kit123308                 |
| Membrane & filling sol'n kit123300   | Themstalle dap lite                    |
| 9V Alkaline Battery130026            |  |
| Manual                               | Cable Extension:                       |
| Mailual130030                        | Extra cable, per metre130040           |
|                                      | Computer Interface:                    |
|                                      | Serial cable for computer130041        |
|                                      | Serial to USB adaptor cable130087      |
|                                      | WinTPS Software for Windows130086      |
|                                      | Baurar anti-mar                        |
|                                      | Power options:                         |
|                                      | 12V Solar Panel                        |
|                                      | 12V Car Cigarette lighter lead.130046  |
|                                      | 12V Clip lead, separate battery.130052 |
|                                      | Carry case:                            |
|                                      | Aluminium Carry Case130059             |



Download this Specification Sheet in PDF format.



Download the full colour WP Series Brochure (832KB PDF).



Download the handbook for this instrument.

#### WP-82Y

Hint: Right click on a link, then select "Save Target As..." or "Save Link As..." to save the file to your own computer.

If you do not have Adobe Acrobat in your computer, a free Acrobat Reader can be downloaded by clicking on the following link.



TPS reserves the right to change any part of this specification without notice. Version 2.0

Copyright © 2002 TPS Pty Ltd



Last modified: January 23, 2009