



HA5PD Atom A10B 5 Litre B & S Class Autoclave



The Atom A10B is an ultra-fast compact autoclave that uses dry vacuum. It adopts **imported high-quality parts** including a **German** vacuum pump and an **Italian** water pump.

The **system** ensures optimal drying, while the **patented independent steam generator** guarantees thorough sterilisation. The autoclave features **intelligent load detection** for energy efficiency, a **large storage capacity** for up to **30,000** records, and comprehensive safety measures including **automatic water quality monitoring** and emergency stop functions. The HA5PD delivers reliable, **high-quality sterilisation** in a **user-friendly design**.

- Fast Cycle Time From 11 Minutes**
- 9 Programs:** Cycle Parameters Can Be Customised To Meet Various Needs
- User Friendly Design:** Intuitive design combined with a 3.5" LCD display.
- Large Storage Capacity:** Can Store Up To 30,000 Sterilisation Records
- Intelligent Load Detection:** Calculates & Uses The Least Amount of Resources
- Additional Features**

 - 3x Pre-Vacuum
 - Pre-Heat Feature
 - External Water Tank
 - Intelligent Load Detection
 - Embedded Control System
 - Water Quality Monitor
 - Intelligent Error Detection
 - Built-In Large Memory
 - 2x Trays 300x190x23mm
 - Custom Program
 - Software Upgrade with USB
 - Preset Timer
 - Auto Safety Door
 - Emergency Functions
 - Power Off Protection
 - Easy Clean Jog-Dial Knob

High Quality Imported Parts

The series boasts imported high-quality parts, including a German Thomas vacuum pump (that can achieve a vacuum level of -0.90bar) and Italian solenoid valves and water pump, provide superior sterilization and maximum preservation for your instruments.



Optional External Printer

An optional Hatmed cycle record external printer can be easily connected at any time. No service technician needed.

Cycle Durations (1kg Load & Including Drying Time)

GENI21	GENI34	134+	Quick B	Quick S	Prion	Fabric	user1	user2
-	19 min	-	13 min	10 min	-	-	-	-

Visit Our Website

