

PSU-20i, Multifunctional Orbital Shaker

DESCRIPTION

Shaker PSU-20i provides three motion types: orbital, reciprocal and vibrating, which can be performed separately, pairwise and sequentially in repeated cycles. Shaker is designed for applications both in small specialized laboratories and in large multidisciplinary laboratories. PSU-20i is an ideal instrument for laboratories conducting research in biopharmaceutics and biomedicine.

Shaker PSU-20i is noiseless and reliable in operation, incorporates a direct drive system and brushless motor with a guaranteed service life up to 35,000 working hours. The use of direct drive and brushless motor allows for continuous mixing up to 7 days and ensures reliable operation for more than 2 years.

A choice of nine (9) different interchangeable platforms provides possibility of performing various procedures and techniques. Special attention should be paid to a multilevel platform, which allows accommodation of a large number of various microplates, Petri dishes, cultural bags and other low containers.

Shaker can be used in cold rooms or incubators, operating at ambient temperature range +4°C to +40°C.



SPECIFICATIONS

| | |
|-----------------------------------|---|
| Speed control range | 20-250* RPM (increment 5 rpm) * max. speed depends on the load and vessels' shape |
| Digital time setting | 1 min–96 hrs / non–stop (increment 1 min) |
| Timer sound signal | + |
| Digital speed control | + |
| Maximum continuous operation time | 168 h |
| Orbit | 20 mm |
| Maximum load | 8 kg |
| Overall dimensions (W×D×H) | 410x410x130 mm |
| Weight | 11.7 kg |
| Input current/power consumption | 12 V, 3.2 A / 40 W |
| External power supply | Input AC 100–240 V; 50/60 Hz; Output DC 12 V |

ACCESSORIES

CAT. NUMBER

| Without platform | Without platform |
|------------------|---|
| BS-010145-ACI | 230VAC 50/60Hz Euro plug |
| BS-010145-ACQ | 230VAC 50/60Hz UK plug |
| BS-010145-AC4 | 230VAC 50/60Hz AU plug |
| BS-010145-ACJ | 100VAC 50/60Hz US plug, 120VAC 60Hz US plug |
| BS-010145-CK | IQ OQ document |
| BS-010145-DK | PQ document |



UP-330
BS-010145-AK
platform

Universal platform with adjustable bars can accommodate laboratory glassware of different shapes.



P-30/100
BS-010135-BK
platform

Platform with clamps for flasks.



P-16/250
BS-010135-CK
platform

Platform with clamps for flasks.



P-9/500
BS-010135-AK
platform

Platform with clamps for flasks.



P-6/1000
BS-010135-DK
platform

Platform with clamps for flasks.



PP-20/4
BS-010126-EK
platform

Flat platform with non-slip rubber mat can accommodate various low profile containers.



PP-20/3
BS-010126-DK
platform

Flat platform with non-slip rubber mat can accommodate various low profile containers.



PP-20/2
BS-010126-CK
platform

Flat platform with non-slip rubber mat can accommodate various low profile containers.



PP-20
BS-010126-BK
platform

Flat platform with non-slip rubber mat can accommodate various low profile containers.



UP-168
BS-010135-JK
platform

Universal platform with clamps can accommodate flasks or bottles of different volume sizes. Clamps are not included with platform and need to be ordered separately.



SPML
BS-010135-MK
double-sided adhesive strips

Double-sided adhesive strips. **SPML** is compatible with **UP-168** platform, that fits both on **PSU-20i** orbital shaker and **inES-20/60, ES-20/80** Shakers-Incubators.



TR-44/15
BS-010135-LK
rack

Adjustable angle test tube rack for **UP-168**



TR-21/50
BS-010135-KK
rack

Adjustable angle test tube rack for **UP-168**



FC-50
BS-010126-MK
clamp

Clamp 50 ml - Ø50 mm for **UP-168**



FC-100
BS-010126-HK
clamp

Clamp 100 ml - Ø65 mm for **UP-168**



FC-250
BS-010126-JK
clamp

Clamp 250 ml - Ø85 mm for UP-168



FC-500
BS-010126-LK
clamp

Clamp 500 ml - Ø105 mm for UP-168



FC-1000
BS-010126-IK
clamp

Clamp 1000 ml - Ø130 mm for UP-168



FC-2000
BS-010126-NK
clamp

Clamp 2000 ml - Ø165 mm for UP-168