

**HIFU TECHNICAL SPECIFICATIONS**

Energy Type	HIFU (High Intensity Focused Ultrasound)
Frequency	4Mhz
Cartridge	Face: 1.5mm, 3mm, 4.5mm
	Body: 6mm, 8mm, 10mm, 13mm, 16mm
Gear Lines	Multi-lines Selectable
Energy Output	0.2 - 3.0J
Operate Mode	Professional mode & Smart mode
Operate Interface	9.7" True Color Touch Screen
Power Supply	AC 110-230V, 50/60Hz
Dimensions	350 x 42 x 22mm (W x D x H)
Weight	6.5kg

**8D 11 LINER**

**HIFU**  
HIGH INTENSITY  
FOCUSED ULTRASOUND




Find our more about HIFU

0414 970 019 07 5577 9881

[www.mmmedicalaesthetics.com.au](http://www.mmmedicalaesthetics.com.au)

or book a consultation with your local specialist at:



# HIFU HIGH INTENSITY FOCUSED ULTRASOUND

## What is HIFU?

HIFU (High Intensity Focused Ultrasound) is cutting-edge non-invasive technology, by the ultimate lifting and contouring treatment that restores youth for face and neck by delivering ultrasound energy into the targeted region of the skin stimulating and formulating collagen regeneration, the precision in delivery of a high density of energy at temperatures of 65-75° Celcius, triggers neo-collagenesis naturally in the skin.

TGA registry of medical devices ARTG # 357130



Featured in June 2019 issue of Australian WHO magazine. It is designed for anti-aging, face lifting, body contouring and sculpting without surgery. The ApoloMed V3 System uses 8D HIFU technology allowing to target 8 different depths.

HIFU is NOT like Laser, Radio Frequency, IPL, needling, or any other surgical, or non-surgical, 'face lift' skin rejuvenation procedure. HIFU is the next generation in advanced facial rejuvenation with deeper penetration, visible longer lasting results. AND most importantly, NO damage to the skin surface. Latest V3 version of ApoloMed makes it one of the fastest HIFU on the market.

## Benefits of HIFU



- Lift and tighten eyebrows
- Reduce fine lines
- Lift and firm the chin/jaw area
- Lift and tighten the cheeks
- Reduce nasolabial folds
- Eyelid lifting
- Lift and tighten the neck area



- Cellulite reduction
- Stretch mark reduction
- Fat reduction
- Body contouring

## Smart Pre-Set Treatment Protocols

You can adjust the settings in PROFESSIONAL MODE or you can use the intuitive touch screen and select the required programmes. The device will automatically give pre-set recommended therapy protocols for each individual precise application.




## HIFU Treatment Handle & Cartridge

- Auto-detected handle
- Multi-line HIFU with lines adjustable for precise treatment
- Facial cartridge & body cartridges for selection:
  - » Face - 1.5mm, 3mm, 4.5mm
  - » Body - 6mm, 8mm, 10mm, 13mm, 16mm
- \* 1 line HIFU optional



## Multi-line Hifu Advantages



### Effects of Temperature On Collagen

