

## TRIANGO 60

The compact one that has what it takes



# TRIANGO 60 – your new treatment & minor surgery light



**TRIANGO 60 C**  
ceiling version




**TRIANGO 60 W**  
wall mount



**TRIANGO 60 F**  
roller stand



**TRIANGO 60 F Battery**  
roller stand



TRIANGO 60	technical data
<b>Fitted with</b>	1x LED-Modul
<b>Luminous power *</b>	60 000 Lux / 1,0 m
<b>Colour temperature *</b>	fixed value 4 700 K
<b>TRIANGO 60-1 F</b>	changeable value
<b>TRIANGO 60-3 F</b>	3 700 / 4 300 / 4 700 K
<b>Lighting field 1,0 m*</b>	ø 18 cm
<b>Depth of illumination *</b>	140 cm
<b>Colour rendering index</b>	Ra > 93
<b>Operation equipment</b>	Electronic converter
<b>Voltage</b>	100-240 V; 50/60 Hz
<b>Luminaire body</b>	Polyamide (PA)
<b>Power consumption</b>	< 30 W
<b>Usage</b>	Touch panel on cardanic system
<b>Technology</b>	Single-pole secondary
<b>Balance of articulation joints</b>	Spring (weight compensation)
<b>Class of protection</b>	I
<b>Protection rating</b>	IP 43 (illumination head) IP 20 (UPSmedv Pack)
<b>Standards met</b>	EN 60601-1, EN 60601-2-41

Special features	
<b>TRIANGO 60-1</b>	<ul style="list-style-type: none"> <li>Continuously dimmable</li> </ul>
<b>TRIANGO 60-3</b>	<ul style="list-style-type: none"> <li>Continuously dimmable</li> <li>3 colour temperatures</li> </ul>
<b>TRIANGO Fokus 60-1</b>	<ul style="list-style-type: none"> <li>Continuously dimmable</li> <li>Focusable</li> </ul>
<b>TRIANGO 60-1 F Battery</b>	<ul style="list-style-type: none"> <li>Continuously dimmable</li> <li>UPSmed Pack</li> </ul>
<b>Mounting</b>	<ul style="list-style-type: none"> <li>Ceiling mount</li> <li>Wall mount</li> <li>Roller stand</li> </ul>
<b>Cord length</b>	
<b>TRIANGO 60-1 C</b>	Direct power supply
<b>TRIANGO 60-1 W</b>	Direct power supply
<b>TRIANGO 60-1 F</b>	3 m
<b>TRIANGO 60-1 F Battery</b>	3 m
<b>Weight (net)</b>	
<b>TRIANGO 60-1 C</b>	13 kg
<b>TRIANGO 60-1 W</b>	12,5 kg
<b>TRIANGO 60-1 F</b>	19 kg
<b>TRIANGO 60-1 F Battery</b>	31 kg
<b>Accessories</b>	<ul style="list-style-type: none"> <li>Sterilizable handle</li> <li>Disposable cover for handle</li> </ul>

**Versatile**  
versions with focusable  
or colour changeable  
illumination field

**Homogeneous light field**  
thanks to unique  
diamond optic

**Easy cleaning**  
streamlined design  
and the removable  
handle

**Hygiene made simple**  
good design does without  
unnecessary details and  
attaches importance to  
closed building structures

**Can be used everywhere**  
TRIANGO 60 is suitable  
for the versatile daily  
routine in family practices  
and clinics as well as in  
gynecology, dermatology  
or veterinary medicine



**Ergonomic handling**  
easy alignment for  
right- and left-handed



**Intuitive operation**  
thanks to an intuitive  
touch panel on the  
cardanic, the illumination  
from 60 000 lux at 1 m  
can be infinitely adjusted

Order number: TRIANGO 60-1	
<b>TRIANGO 60-1 C</b>	D16.250.000-00813741 D16.253.000-00814312 - USA
<b>TRIANGO Fokus 60-1 C</b>	D16.252.000-00814311 D16.255.000-00814314 - USA
<b>TRIANGO 60-1 W</b>	D16.256.000-00813742 D16.274.000-00814327 - USA
<b>TRIANGO Fokus 60-1 W</b>	D16.258.000-00814316 D16.276.000-00814329 - USA
<b>TRIANGO 60-1 F</b>	D16.262.000-00813744 - CH D16.259.000-00813743 - Schuko D16.271.000-00813747 - UK D16.265.000 - USA
<b>TRIANGO Fokus 60-1 F</b>	D16.264.000-00814320 - CH D16.261.000-00814318 - Schuko D16.273.000-00814326 - UK D16.270.000-00814322 - USA
<b>TRIANGO 60-1 F Battery</b>	D16.279.000 - CH D16.278.000 - Schuko D16.282.000 - UK D16.280.000 - USA

Order number: TRIANGO 60-3	
<b>TRIANGO 60-3 C</b>	D16.251.000-00814310 D16.254.000-00814313 USA
<b>TRIANGO 60-3 W</b>	D16.257.000-00814315 D16.275.000-00814328 USA
<b>TRIANGO 60-3 F</b>	D16.263.000-00814319 - CH D16.260.000-00814317 - Schuko D16.272.000-00814325 - UK D16.266.000-00814321 - USA



\* -10% / +20% tolerance



ENG | © Derungs Licht AG · D80.262.000-00814394 · 06/2023 · Subject to modifications · Printed in Switzerland



Sydney | Melbourne | Brisbane | Perth

☎ 1300HPAUST  
✉ info@hpaust.com  
🌐 www.hpaust.com



DB020V123