

| item # | |
|-----------|--|
| model # | |
| project # | |
| sis# | |
| aia # | |



HHT081E Hot holding trolley

CONSTRUCTION FEATURES

- Tightness chamber with radiuses corners
- All-around rubber bumpers
- Total thermic insulation with rock or glass wood
- Long lasting front and door seals made up of food glade of high heat resistance
- Removable side racks to facilitate cleaning
- Static heating provided by low consumption wire heating element that coils up all the chamber
- Ergonomic and fully built-in door handle with magnetic closure
- Mounted on four 125 mm diameter castors, two of which with brake
- Ergonomic handle for pushing and guiding
- Easy access to facilitate maintenance and repair

FUNCTIONAL FEATURES

- Electronic control of the temperature
- Operating temperature 30°-120°C
- Two adjustable humidity vents on the door
- Chamber with safety thermostat

STANDARD SUPPLY

• Removable GN 1/1 tray racks

OPTIONS & ACCESSORIES

☐ Pass-through design





TECHNICAL INSTALLATION DIAGRAM






Adjustable vent for release of excess humidity







Overall dimensions (W x D x H) - mm

550 x 735 x 1010

Trays capacity

8 x GN 1/1

Tray max. height [mm]

8 x 65 (h)

3 x 150 (h)


2 x 200 (h) + 2 x 65 (h)

Power kW

1

Power supply

AC 230 V / 50 Hz



- A Display
- B ON/OFF switch
- C Temperature decrease key
- D Temperature increase key
- E START/STOP key

MODULINESRL