


DERM 101

Electrosurgical Generator



The Derm 101 is an economical, 10 watt high frequency desiccator, thoughtfully designed to give practitioners the ability to perform in-office, minor skin procedures such as the removal of skin tags, benign lesions and premalignant lesions. These Bovie units allow practitioners to provide better patient care in the office, at a sensible price, saving the patient time and money, while increasing their practice revenue.

Affordably priced to minimize the facility's expense and maximize their ROI.

Ten (10) watts of monopolar power which are adjustable in 1/10th watt increments.


The thoughtfully designed unit allows Practitioners the ability to perform minor skin procedures with an easy-to-operate device, to increase their practice revenue.

Packaged complete and ready to use. By the time the practitioners utilize all 18 electrodes they will have paid for the unit, twice.

The Derm 101 is backed by Bovie's standard four (4) year warranty.



DERM 101 ELECTROSURGICAL GENERATOR



STANDARD EQUIPMENT

DERM 101 electrocautery generator
 A902 handpiece
 A910 (2) non-sterile disposable handpiece sheaths*
 A804, A806 (5 ea) non-sterile dermal tips
 A805, A807 (2 ea) sterile dermal tips
 A806DE (2) non-sterile Derm-Elite® blunt dermal tips
 A807DE (2) sterile Derm-Elite® blunt dermal tips
 A837 wall mount kit*
 110 VAC Hospital-grade power cord*
 User's guide (MC-55-173-001)*

* Not Pictured



A902



A804, A805



A806, A807



A806DE, A807DE

COMPLEMENTARY PRODUCTS †



A813
Table Top Stand †



ES20
Ball Electrode †



ES02
Needle Electrode †



A910ST
Sterile Handpiece Sheath †



The Derm 102 has a bipolar mode going up to 10 watts



A803
Footswitch †



A827V
Forcep Cable †



A824
Reusable Bipolar Forceps †

† Sold Separately

PRODUCT SPECIFICATIONS

DIMENSIONS

Height: 20.8cm (8.2 in.)
 Width: 18.4cm (7.2 in.)
 Depth: 6.9cm (2.7 in.)
 Weight: < 1.4 kg (< 3 lbs.)

OUTPUT POWER

To 10 watts (0-10 watts in 1/10th watt increments on both monopolar and bipolar)

OUTPUT FREQUENCY

550 kHz

LINE VOLTAGE

DERM 101: 100-240 VAC
 DERM 102: 100-240 VAC

LINE FREQUENCY

50 – 60 Hz

WARRANTY

Four Years