

# Westlab Digital Stirred Water Baths

Codes 663-898, 663-899, 663-900, 663-903, 663-904







## Westlab Digital Stirred Water Baths

Westlab's Stirred Water Baths feature a digital PID temperature controller and are designed for immersion of flasks, bottles and racks in an accurate temperature environment throughout the water bath. The stainlesssteel tank is housed in a sturdy outer case and is supplied complete with a stainless-steel shelf which provides even water circulator and temperature stability.

The painted surfaces feature a tough antibacterial finish with good chemical resistance. Easy to use controls which are wipe clean and have an antibacterial finish. Immersed components are corrosion resistant. The efficient stirrer is quiet in use and provides excellent temperature stability. Indication of heating, over temperature alarm and timer running.

When a low liquid level is detected a "FILL" message automatically appears and heating is suspended. Once refilled, heating is restored, and temperature control resumes automatically. Over and under temperature alarms automatically protect samples in the water bath.

#### **Product Features**

- Digital LED Display
- Stainless Steel Tank
- Ambient + 5°C to 99°C
- Stainless Steel Perforated Shelf
- Made in the United Kingdom

#### Australia

1800 358 101 sales.au@westlab.com www.westlab.com.au Canada 1 877 822 1455 sales.ca@westlab.com www.westlab.com

#### New Zealand

+64 9 553 3677 sales.nz@westlab.com www.westlab.co.nz

#### **PRODUCT CODES**

663-898 663-899 663-900 663-903 663-904

#### United States

646 568 5391 sales.us@westlab.com www.westlab.com

### **Product Specifications**

	663-898	663-899	663-900
Tank Capacity	14L	22L	28L
Temperature Range	Ambient + 5°C to 99°C		
Temperature Alarm	Digital LED Display - Under/Over Temperature Alarm is Automatically Set 4°C Above & 4° Below Set Point		
Temperature Control	PID Digital, LED Display, Resolution of 0.1°C		
Water Level Range	130mm Maximum		
Sensitivity	± 0.05°C		
Uniformity	± 0.01°C		
Timer	Visual Indicator & End Message – Variable 00:01 to 99:59 hh:mm		
Heater Power	1,250W		
Voltage	230 V, 50 to 60 Hz		
Internal Dimensions (mm)	219 W x 298 D x 150 H	395 W x 298 D x 150 H	395 W x 298 D x 200 H
External Dimensions (mm)	361 W x 332 D x 170 H	537 W x 332 D x 170 H	537 W x 332 D x 290 H

#### Accessories

	663-903	663-904
Flat Lid,	Suits 14L Bath	Suits 22L & 28L Baths
Stainless Steel	(663-898)	(663-899 & 663-900)



#### Australia

1800 358 101 sales.au@westlab.com www.westlab.com.au Canada 1 877 822 1455 sales.ca@westlab.com www.westlab.com

#### New Zealand

+64 9 553 3677 sales.nz@westlab.com www.westlab.co.nz

#### United States

646 568 5391 sales.us@westlab.com www.westlab.com