




Choosing Your Ideal UV Oven

FEATURE	CURIE Plus		CURIE		UV Box	
Resin Validation	Class II Resins		Class II Resins		Non-Biocompatible Resins	
Resin Library Updates	Via Online Server		Via SD Card		-	
Nitrogen Compatibility	NFINITY and N ₂ Tank		-		-	
Wireless Integration	SOL Plus and SOL		-		-	
Door Opening Mechanism	Automatic		Manual		Manual	
User Interface	Digital Touchscreen		Analog Controls		Analog Controls	
Chamber Dimensions	20 (L) x 15 (W) x 6 (H) cm 7.9 (L) x 5.9 (W) x 2.4 (H) in		14 (L) x 14 (W) x 8 (H) cm 5.5 (L) x 5.5 (W) x 3.1 (H) in		15 (L) x 17 (W) x 7 (H) cm 5.9 (L) x 6.7 (W) x 2.8 (H) in	
Chamber Capacity	8 Full Arches		4 Full Arches		4 Full Arches	
LED Lights	65		31		12	